

Features

- UL[®] 1069 Listed
- Simple and flexible operation
- Call-placed indicator
- Call cancel at point of origin
- Flame-retardant (UL[®] 94V-0) plastic faceplate
- 1.1" wide pull down lever

Description

The SF155B Emergency Station is for use in any location where activation of an emergency signal is required. All electronic components are mounted on a circuit board. The specially designed and mounted LED is completely sealed in plastic.

Due to the flexibility of its design, it may be used as a pull-cord emergency station, or a pull-down activated emergency station. The pull cord supplied may be used for emergency call activation, or if desired, the large 1.1" red pull-down lever may be used.

Listings



UL[®] 1069 listed; UL[®] File Number E71599.



SF155B Emergency Station

Specifications

Dimensions:	Height:	4.5"	(114 mm)
	Width:	2.8125"	(72 mm)
	Depth:	1.625"	(41 mm)
	Projects:	0.6875"	(17 mm)
		from mounting surface (including pull-down lever)	
Construction:	Flame-retardant (UL [®] 94V-0) plastic faceplate. Switch and electronic components are circuit board mounted.		
Connections:	Plug-in connectors.		
Housing:	Single gang ring, or single gang ring with double gang box.		

Required Components

Tek-CARE[®] NC110, NC150 or NC200 Nurse Call System